




View in direction
of arrow (A)




CN21 pin layout





View in direction
of arrow (B)



CN20 pin layout



Pin assignment on
Ethernet connector



Notes for cleanroom type

*1 Recommended suction air flow rate: 25 to 30 liters/min.
Recommended blower: VFZ081PN
(manufactured by TERAL INC.)
The cleanroom type requires ventilation inside the robot.
Exhaust air from the air vent provided in the back of the robot base.

*2 Dimension D at point of use
(distance from the rotation center of the first axis)
D = 300 mm

AIR No.	Air piping joint	Maximum allowable pressure
AIR 1,2	φ4, PT1/8	0.59 MPa
AIR 3,4	φ6, PT1/4	